PRODUCT INFORMATION

Spherical Beamforming Systems

based on Spherical Beamforming Type 8606

Spherical Beamforming is one of a suite of systems developed for noise source identification. Based on one simple measurement, the system provides a complete, omnidirectional noise map in any acoustic environment.

Unlike other measurement methods that only map part of the surroundings, spherical beamforming uses a spherical array of microphones and cameras to simultaneously measure noise levels and take pictures in all directions. When the results are displayed, the noise measurements are superimposed on the pictures to create an acoustic map.

Spherical beamforming does not make any assumptions about the nature of the acoustic environment and can therefore be used in both free-field and reverberant environments. The system is commonly used to make overview maps in confined and semi-damped spaces such as vehicle, train and aircraft cabins.



Uses, Features and Benefits

Uses

- Wide frequency range measurements
- Vehicle interior noise measurements
- · Squeak and rattle testing
- End-of-line wind box vehicle testing
- Aircraft and train cabin noise measurements
- Industrial plant noise measurements
- Source location in rooms and factory halls

Features


- · Quick snapshot measurement
- · Omnidirectional coverage
- Independent of acoustic environment
- Two algorithms implemented:
 - Filter and Sum (FAS), patent pending
 - Spherical Harmonics Angularly Resolved Pressure (SHARP)

Benefits

- Saves time via rapid evaluation of noise problems
- · Easy to use
- · Easy to mount inside a vehicle
- · Robust array with many applications
- Boosts low-frequency resolution with FAS

Measurement and Calculation


Fig. 1Car seat fixture for spherical array



The measurement is performed using an array of 36 or 50 microphones mounted on the surface of a hard sphere. The microphone positions on the sphere are numerically optimized to maximize the dynamic depth of the map. The sphere is usually placed at a typical (sound) impact position, for example, in the driver's seat of a vehicle using the car seat fixture for spherical array (Fig. 1).

The calculation decomposes the observed sound field into its spherical harmonic components and then estimates the directional contributions by recombining these spherical harmonics.

Fig. 2
Typical 36-channel
system. Spherical
beamforming systems
are supplied as
customer-specified
projects



Calibration

Fig. 3Calibration of the spherical array



The spherical array and complete measurement system are easily calibrated using Pistonphone Type 4228 with a single-channel "stethoscope" adaptor (Fig. 3).

The angular resolution provided by the spherical beamforming algorithms FAS and SHARP are roughly the same (see Table 1). However, FAS provides considerable improvement in the maximum side lobe (MSL) level and, in conjunction with a low-frequency boost (LFB) algorithm, increases the angular resolution at low frequencies.


Table 1 Comparison of resolution (-3 dB), in degrees, between FAS and SHARP beamforming for a sphere with diameter 19.5 cm

Algorithm	100 Hz	200 Hz	500 Hz	1 kHz	2 kHz	4 kHz	6 kHz	8 kHz	10 kHz	12 kHz
FAS (36 and 50 ch.)	145	105	68	48	32	24	16	13	10	8
FAS with LFB (36 ch.)	110	95	68	48	32	24	16	13	10	8
FAS with LFB (50 ch.)	85	70	52	48	32	24	16	13	10	8
SHARP (36 and 50 ch.)	145	105	68	48	32	24	16	13	10	8

The error-free dynamic depth, or MSL level, decreases with frequency, but for FAS with the 50-channel array, it is greater than 6 dB up to 12 kHz, and for the 36-channel array, greater than 6 dB up to 7 kHz. Therefore, the bands of use of spherical beamforming are set towards low frequencies by resolution and towards high frequencies by dynamic depth, with a range from 100 to 12800 Hz.

The SHARP algorithm has a limited MSL level at higher frequencies, so it is recommended to use FAS above 6.4 kHz.

Fig. 4 Comparison of the MSL levels for the SHARP and FAS algorithms. Left: 50-channel array, Right: 36-channel array



Application Examples

Typical applications for spherical beamforming include:

- · Vehicle interior noise
- · Wind tunnel measurements on vehicles
- · Aircraft cabin noise
- Rooms
- Industrial plant noise

See Figures 5 through 8 for examples of these applications.

Fig. 5 Combination of the spherical array (**left**) with the hand-held conformal holography system (**right**) used to investigate noise from a ventilation system




Fig. 6
Spherical
beamforming used to
investigate noise
(2 – 4 kHz) from a
locking mechanism
during door slam



Fig. 7 Spherical beamforming used to investigate a hole in the upper seal of a passenger door at 80 mph. Left: 600 – 4500 Hz: This broad-frequency-range map does not localize the hole in the seal well Right: 1400 – 1500 Hz: This frequency range accurately pinpoints the hole in the seal







Fig. 8
Spherical
beamforming used to
investigate noise in
the gangway of a
high-speed train. The
map shows the
1600 Hz third-octave
band



Configuration

OPERATING SYSTEM REQUIREMENTS

Microsoft® Windows® 8.1 Pro or Enterprise (x64), Windows® 7 Pro, Enterprise or Ultimate (x64)

OTHER SOFTWARE REQUIREMENTS

Microsoft® Office 2013

Microsoft® SQL Server® 2012 Express (SP 2) (included with PULSE)

COMPUTER CONFIGURATION/DATA ACQUISITION FRONT ENDS

As for PULSE, see System Data BU 0229

PREREQUISITES

- PULSE 7700/7770/7771
- PULSE Acoustic Test Consultant Type 7761

Software Specifications for PULSE Spherical Beamforming Type 8606

Measurement			
Monitor view	Yes (for single camera)		
Data	Time or spectral		
Optical picture	Take or reuse		
Automatic processing	Store automatically, Calculate automatically, Selectable calculation		
Data Management			
Databases	Multiple simultaneous		
Inspect metadata	Yes		
Search on metadata	Yes		
Change metadata	Yes		
Calculation			
Multi core support	Yes		
Target mesh type	Spherical		
References	Physical		
Methods	FAS (with low-frequency resolution boost) and SHARP		
Filtering	Frequency, Order		
Domains	Stationary, Quasi-stationary, Transient		
Function	Pressure Contribution, Pressure, Intensity		
Index dimensions	Time, RPM, Angle		
User Interface			
User levels	Basic and Advanced, User-defined		
Defaults	User-defined		
Contribution Analysis			
Sound Power	Area, Component		
Map Displays			
Number of displays	1 × 1 to 4 × 4		
Alignment of displays	Data, Frequency, Index, Colour scale		
ayback Measured and calculated Points			
Reporting			
Cut and Paste	One view, All views		
Movie file generation	Animation driven, Audio driven		
Microsoft® Word report generator	rosoft® Word report generator Across frequencies, Across indices		

Hardware Specifications for Spherical Array WA-1565

36-CH. SPHERICAL ARRAY Frequency Range

• 200 - 6400 Hz with SHARP

100 – 6400 Hz with FAS
 Diameter: 19.5 cm (7.68 in)
 Weight: 5 kg (11.02 lb)

50-CH. SPHERICAL ARRAY Frequency Range

• 200 – 7000 Hz with SHARP

• 100 - 12800 Hz with FAS

Diameter: 19.5 cm (7.68 in) **Weight:** 5 kg (11.02 lb)

Typical 36-channel System

PULSE SOFTWARE FOR SPHERICAL BEAMFORMING

1 × Type 8606-X	PULSE Spherical Beamforming
1 × Type 7770-X16*	PULSE FFT Analysis, Unlimited Channels
1 × Type 7708-X16*	PULSE Time Data Recorder, Unlimited Channels
1 × Type 7761-X*	PULSE Acoustic Test Consultant

SOFTWARE MAINTENANCE AND SUPPORT

SOFTWARE MAINTENANCE AND SUPPORT				
1 × M1-8606-X*	Annual Software Maintenance and Support Agreement			
	for PULSE Spherical Beamforming			
1 × M1-7770-X16 [*]	Annual Software Maintenance and Support Agreement			
	for PULSE FFT Analysis, Unlimited Channels			
1 × M1-7708-X16 [*]	Annual Software Maintenance and Support Agreement			
	for PULSE Time Data Recorder, Unlimited Channel			
1 × M1-7761-X*	Annual Software Maintenance and Support Agreement			
	for PULSE Acoustic Test Consultant			

DATA ACQUISITION HARDWARE

DATA ACQUISITION HARDWARE			
1 × Type 7201-G	Dell™ High-end Notebook		
1 × Type 3660-C-100	LAN-XI Front-end Frame with GPS, 5-module		
3 × UA-2112-120	LAN-XI Front Panel with Array Connectors, 2 × LEMO (7		
	pin) connectors		
3 × Type 3053-B-120	12-channel Input Module LAN-XI 25.6 kHz (CCLD, V),		
	including Front Panel UA-2107-120		
× Type 2831-A	Battery Module		

SPHERICAL BEAMFORMER INCLUDING ACCESSORIES

$1 \times WA-1565-W-020^{\dagger}$	Spherical Array, &	Ø 195 mm/36	positions/12 cameras
	includes Splitter	Box WB-3477	

1 × WL-1297-W-005[‡] Bundle of 6 cables in braided sleeve with individual numbering, 7-pin LEMO connectors, length 20 m

 $1 \times$ WA-1647-W-001 † Car Seat Fixture for Spherical Array $1 \times$ WA-0728-W-004 † Single-channel Pistonphone Adaptor

1 × Type 4228 Pistonphone

WQ-2552 Small Computer Systems Interface (SCSI) Cable, 5 m

Optional Accessories

SOFTWARE

1 × Type 7770-X16	PULSE FFT & CCB Analysis, Unlimited Channels
1 × Type 7771-X16*	PULSE CCB Analysis, Unlimited Channels
BZ-5635-X*	PULSE Array Acoustics Quasi-stationary Calculations
BZ-5636-X [*]	PULSE Array Acoustics Transient Calculations
BZ-5637-X [*]	PULSE Array Acoustics Conformal Calculations
BZ-5638-X [*]	PULSE Array Acoustics Sound Quality Metrics
BZ-5652-X*	PULSE Array Acoustics External Plug-in Manager
HARDWARE	
WA-1565-W-021 [†]	Spherical Array for 50 Channels, includes Splitter Box WB-3477
WL-1297-W-006 [‡]	Bundle of 9 cables in braided sleeve with individual numbering, 7-pin LEMO connectors, length 20 m
WA-0728-W-007 [†]	Single-channel Pistonphone Adaptor, with stethoscope for spherical array Microphones Type 4959
WA-1647-W-001 [†]	Car Seat Fixture for Spherical Array
WA-1678	Optional Support for fixture between car seats
WQ-2691	Tripod, heavy duty, 0.94 m-2.17 m, max. load 12 kg

TRANSDUCERS

Type 4959 Short 20 kHz Array Microphone

SOFTWARE MAINTENANCE AND SUPPORT

Available for all software packages

See the PULSE Software Maintenance and Support Agreement Product Data (BP 1800) for further details

Brüel & Kjær and all other trademarks, service marks, trade names, logos and product names are the property of Brüel & Kjær or a third-party company.



^{*} X indicates the license module, either N: Node-locked or F: Floating

[†] Ordered via Project Sales

[‡] Available in different lengths, inquire when ordering